

ULTRASONIC 4

CLEANER FOR ALUMINUM PARTS

ULTRASONIC-4 is formulated to be used as detergent for cleaning parts and tooling dip aluminum ultrasonic cleaning machines.

With its balanced formulation has properties suitable for removing plaque embedded grease, oil or any other kind of stubborn dirt, preventing them from re-depositing on the pieces and clean.

DOSAGE AND METHOD OF USE

ULTRASONIC-4 may be used diluted in water ultrasonic tank at a rate between 2 and 5%.

TECHNICAL CHARACTERISTICS

COLOR	BLUE
ASPECT	TRANSPARENT LIQUID
ODOR	CHARACTERISTIC
DENSITY	1,12 +/- 0,05 g/cm ³
pH	10,9 +/- 0,5

CONTAINS

5 % – 15 %	Non ionic surfactants
> 5 %	Anionic surfactants
> 5 %	Phosphates
> 5 %	EDTA (tetrasodium etilendiamintetracetate) and salts thereof

This product meets the existing legislation on biodegradability and the Sanitary Technical Regulation on Detergents.